

Flexsol Liner Specification

Product U301C

Issue: 2 20/04/2016



Description: Six Layer 1000 Litre Top fill / Bottom Discharge Liquid Liner. 2" BSP fill x 2" Square discharge with clip, Tinted LLDPE

Application: This liner is specified for use with the CHEP Pallecon Solutions Ultra or iConic system or similar IBC's, for applications where fill or exposure temperatures do not exceed 80°Centigrade. This liner meets European and FDA requirements for food contact materials.


The Finished Product View (when unfolded)

All measurements inside welds

The first liner of any batch should be quality checked and measured against Flexsol procedures manual module 8


From discharge gland side

(Not to scale)



From fill gland side

(Not to scale)



Parts list

| | | |
|---------------------------|---------------------------------|----------|
| Fill | 2" Fill Gland | B20.401 |
| | 2" BSP Blue Gland | |
| | 2" BSP Yellow Screw Cap | |
| Discharge | 2" Square Gland <i>Blue-Mem</i> | B20.408 |
| | 2" Square Gland | |
| | 2" BSP Red Cap | |
| | 2" Blue Cutter | |
| | <i>Blue</i> Membrane Pe/Pet | |
| 1 Outer film layer | Flexcene Tinted | B10.054 |
| 2 Inner film layer | Flexcene Tinted | B10.054 |
| 3 Contact film lay | Flexcene Tinted | B10.054 |
| Attached | White Ultra CLIP - <i>SOFT</i> | B20.078A |

Folding instructions

FFP001 Standard folding pattern

Packaging spec

FPS01 - Large Flexsol carton

Qty per carton: 10
Qty per pallet: 200 liners
Carton weight: 21Kg
Liner weight: 1.9Kg

Special Instructions

Fittings to be covered with bubble wrap to prevent film damage.

One sheet of Ultra Bubblewrap to be used in top of each box to prevent liners damage.



B20.401



B20.408



B20.078A-soft